

PV:1500 CLAMP

601A1200 CLAMP METER



Key Features

- Handy, compact design that fits perfectly into any everyday working environment
- Shock and impact resistant thanks to robust construction
- Display with 4000 counts
- Rotary switch for measuring mode selection
- Safety per DIN VDE 041-1/EN 61010
- Measuring category CAT IV / 1000 V (CAT III / 1500 V)
- Resistance measurement
- Voltage measurement (AC and DC)
- Current measurement (AC and DC)
- Capacitance measurement
- Frequency measurement
- Diode and acoustic continuity testing
- True RMS value display (TRMS)
- Freezing of measured value (HOLD)
- Switch between minimum, maximum and normal value
- Automatic range selection



APPLICATION

The new PV:1500 Clamp is especially designed for PV installers and O&M technicians to be used in conjunction with the PV:1525 Series: It can be connected to the PV tester via Bluetooth® to wirelessly transmit current measurements which allow power measurements to be logged within the PV:1525 & PV:1525-IV.

An integrated LCD screen means the PV:1500 Clamp can be used fully standalone as well, becoming an integral part of any PV installers toolkit. It's 35 mm jaw opening makes it perfect for use across a wide range of applications not just in PV, e.g. in industry, trade, electromobility.

With protection category CAT IV / 1000 V (CAT III 1500V), the device corresponds to the highest safety category for AC and DC and it is produced in accordance with the latest safety regulations and ensures safe and reliable working.

SCOPE OF DELIVERY

Standard scope of delivery:

- 1 × Current clamp PV:1500 Clamp
- 2 × Measurement cables (1 × red, 1 × black)
- 2 × Batteries (1.5 V, AAA, IEC LR03)
- 1 × Operating instructions

Together, we're making our world a safer place.
Every. Single. Day.

INCLUDED FEATURES

PV:1500 Clamp is distinguished by the following features:

- Bluetooth® for connection to PV:1525
- Current measurement AC/DC up to 400 A
- μ A measurement AC/DC
- Voltage measurement up to 1000 V_{AC} or 1500 V_{DC}
- Inrush current measurement
- Maximum safety thanks to CAT IV / 1000 V (CAT III 1500 V)
- TRMS measurement
- Resistance, capacitance and frequency measurement
- Continuity and diode testing
- Non-contact voltage measurement
- LPF function (low-pass filter)
- Flashlight
- Illuminated display
- Automatic shutdown
- Self-test function


SEAWARD

United Kingdom and Rest of World

+44 1991 587 8730

sales@seaward.com

DACH

+49 911 8602-0

export@gossenmetrawatt.com

Americas

+1 813 886 2775

sales@seaward-groupusa.com

TECHNICAL DATA

Display	LCD; 7 segments, 4-digit display, backlight; Current, voltage, resistance, capacitance, frequency, continuity, diode, polarity (- for negative values), inrush current; NCV, LPF, Hold, Min/Max, Zero, Bluetooth®, automatic switch-off, battery check
LEDs	Flashlight, NCV
Voltage measurement	1 mV _{AC} ... 1000 V _{AC} TRMS, 1 mV _{DC} ... 1500 V _{DC}
Overload protection - high impedance	10 MΩ voltage measurement
Current measurement	Clamp: 0.2 A _{AC} ... 400 A _{AC} TRMS, 0.2 A _{DC} ... 400 A _{DC} Socket: 2 μA _{AC} ... 400 μA _{AC} TRMS, 2 μA _{DC} ... 400 μA _{DC}
Resistance measurement	0 Ω ... 40 MΩ
Capacitance measurement	10 nF ... 100 μF
Continuity test	< 30 Ω acoustic signal Reversing point 0 Ω to 30 Ω (± 20 Ω)
Diode test	0 V ... 1.0 V
Frequency measurement	1 Hz ... 9,99 MHz
Clamp opening	35 mm, oval
Distance of measuring cables	25 mm
TRMS	Yes
NCV (non-contact voltage measurement)	Yes (AC only)
LPF (low-pass filter)	Yes, 1 kHz / -3 dB
Connectivity	For connection to PV:1525 & PV:1525-IV; Bluetooth® 5.0, 2.402 GHz ... 2.48 GHz, +8 dBm maximum
Flashlight	Yes
Automatic shutdown	Yes
Self-test	Yes
Measuring category	CAT IV / 1000 V (CAT III / 1500 V)
Pollution degree	2
Power supply	Batteries, 2 × 1.5 V AAA, IEC LR03
Tested per	IEC 61010-1, IEC 61010-2-032
Dimensions	Approx. 220 × 80 × 42 mm
Weight	Approx. 268 g (without batteries)
Ambient conditions	Operation: 0 °C ... +50 °C, max. 80% relative humidity Storage: -10 °C ... +60 °C, max. 80% relative humidity (without batteries) Elevation: up to 2000 m
FCC	Class B

601A527
Rev. 3 (10/2026)

Together, we're making our world a safer place.
Every. Single. Day.



United Kingdom and Rest of World

+44 1991 587 8730

sales@seaward.com

DACH

+49 911 8602-2

export@gossenmetrawatt.com

Americas

+1 813 886 2775

sales@seaward-groupusa.com

Find your local partner at seaward.com/gb/distributors/