POWERCHECK 1557

The ONLY comprehensive PAT and Installation verification instrument



The PowerCheck 1557 is the only comprehensive PAT and Installation instrument verification system in one rugged, drop-proof enclosure. It tests to BS 7671, BS EN 61557, IET Onsite Guide and IEE Code of Practice. It has full instrument verification against all relevant standards and confirms performance between verifications (this is information required by NICEIC, ELECSA, Corgi and others). PowerCheck tests for Full Earth Continuity, Insulation Resistance, RCD Trip Time, RCD Trip Current, Loop, PE Conductor Current, Touch Current and Flash test verification.

Key Features

- Rugged and robust
- Tests to BS7671 / EN 61577 / IEE Code of Practice
- Confirm performance
- NICEIC & IET compliant
- Colour coded for ease of use
- Compatible with all installation and PAT testers

Ideal Users

- Electricians
- Service engineers
- Electrical contractors



Web: www.seaward.co.uk Email: sales@seaward.co.uk

Seaward

Bracken Hill, South West Industrial Estate, Peterlee, SR8 2SW **Tel:** +44 (0) 191 5863511

Fax: +44 (0) 191 5860227

POWERCHECK 1557 SPECIFICATIONS

SPECIFICATIONS - IINSTALLATION TEST INSTRUMENTS

Earth Continuity Verification

Test current In >200mA indication
Test voltage 4V < Un > 24V indication
Test resistances 0.5ohm and 20hm

Insulation Resistance Verification

Open circuit test voltage: 250V < Un < 375V indication

500V < Un < 750V indication 1000V < Un < 1500 indication

Test current In >1mA into 1000ohm/V

Max test current lk <2mA

Test resistances 0.25Mohm, 0.5Mohm, 1.0Mohm

Earth Loop Verification

Test values Loop, Loop+1ohm, Loop+180ohm

RCD Verification

 Trip current
 10mA, 30mA, 100mA

 Trip Times
 20ms, 40ms, 500ms

Test current multiplier 1/2△n, I△n and 5 I△n verification

Voltage Verification

Test Voltage 240V AC rms test output

PAT FUNCTIONS

Earth continuity verification

Test resistances 0.2ohm and 2ohm

Insulation Resistance verification

Test resistances 500kohm, 1Mohm and 2Mohm

PE Conductor current

Test currents* 0.1mA, 0.25mA and 0.5mA

Flash Test current

Test currents* 0.5mA, 1mA and 1.5mA

ADDITIONAL INFORMATION

Power supply 230V AC ±10%

Dimensions / Weight 210mm x 145mm x 85mm / 1kg

*actual values are dependent upon mains supply voltage. Tabulated values for mains voltages of 210V to 250V are supplied with the instrument.

PowerCheck 1557 part no: 369A910



Seaward test and measurement companies include:



