

Apollo+ Series

The best downloadable PAT testers on the market.



Our world beating **Apollo+** Series can be used to test in accordance with both the IET Code of Practice and BS EN50699 . It now has a Wifi hotspot feature for remote data transfer via any mobile device in order to exchange data when testing in the field.

Straightforward PAT testing with simple data management

Following in the footsteps of Seaward's long line of trusted PAT testers, the Apollo+ Series offer a comprehensive suite of electrical safety tests to enable any workplace appliance to be tested. The Apollo+ also enables point to point testing of fixed appliances.

Risk-based PAT testing

The Apollo 600+ and 500+ have a built-in electrical risk assessment tool that can be used to easily determine a risk-based suggested retest period. For users who are responsible for recording other non-electrical tests or inspections such as fire extinguishers or ladders, the user-configurable test function enables this.

Visual evidence for full traceability

Apollo 600+ has a built-in digital camera enabling images taken during visual inspections and risk assessments to be tagged against records in Seaward's PATGuard 3 software as evidence - making it the most comprehensive and traceable record-keeping system.

Why buy the new Apollo+ Series?

- > Large on-board storage
- > High definition colour display
- > Remote data transfer via hotspot to mobile device from field to office
- > Fixed appliance (point to point) testing
- > User configurable tests - for non-electrical tests and inspections e.g. fire extinguishers and PPE

Apollo+ Series Users:

- > Professional PAT Testers
- > Electrical Contractors
- > Facilities Managers
- > Operations Managers

To see the **Apollo+** Series for yourself, request your live online demonstration today at seaward.com/apolloplus



SEAWARD
GMC-INSTRUMENTS GROUP

T: +44 (0) 191 587 8741 E: sales@seaward.com

TESTED, TRUSTED... WORLDWIDE.

Apollo+ Series

The best downloadable PAT testers on the market.

Total health and safety management

Apollo 600+ features a built-in universal risk assessment tool allowing hazards to be recorded, risk scores to be calculated and corrective actions to be planned and documented easily. For those who have responsibility for health and safety inspections outside of portable appliance testing, the Apollo 600+ also hosts onboard reports for fire detection and emergency lighting - making it an all-in-one solution for the future of health and safety management.

Superb software for total traceability

Apollo+ Series instruments have large internal memories either 50,000, 10,000 or 2,000 slots (600+, 500+ and 400+ respectively) and an additional 2,000 images (600+ only). Their compatibility with Seaward's PATGuard Cloud software means that complete test records, including images, can be easily managed on a PC.

Easily transfer data to a PC remotely using the Apollo Wifi hotspot function* and any mobile phone, tablet or computer or download results onto a USB flash drive (600+ only). Alternatively, transfer data directly using a USB lead when back at the office. Once downloaded to PATGuard Cloud, it is easy to keep track of the history of test and inspections, produce reports, certificates and invoices – offering total peace of mind and quicker, easier management of scheduling inspections and tests.

PATGuard Cloud is a user-friendly cloud-based software that lets you record, store and report on PAT testing, risk assessments and other workplace safety inspections.

- Access your data from any device
- Add multiple users on one account
- Easily schedule retests
- Attach images to records
- Generate professional reports and certificates
- Experience complete compliance and traceability for all your PAT testing results.
- Simple migration from existing PAT software

Further details and free trial can be found at patguardcloud.com

Scan and print QR codes

Seaward's new QR code data system allows more data to be stored in your PAT label barcode including; Asset ID, site, location, last and next test dates. Using Seaward's Test n Tag Elite 2 printer you can now print labels that include our unique QR data code, the Apollo 600+ and 500+ have the ability to read the data contained in the code via our new Bluetooth 2D Elite barcode scanner and populate the fields automatically for quicker retesting without the need for data upload.

With our new QR DATA Viewer app (available for both Android and iOS devices) you can share these benefits with your customers - the app allows end users to scan the labels and see the test information, they can then very easily share the data via email. This functionality allows duty holders and end users to keep better track of faulty items.

**WiFi hotspot feature does not require internet connection*

To see the **Apollo+** Series for yourself, request your live online demonstration today at seaward.com/apolloplus

T: +44 (0) 191 587 8741 E: sales@seaward.com

TESTED, TRUSTED... WORLDWIDE.

Electrical Test Functions:


- > Low current earth continuity test (with Zap circuit) guaranteeing accurate measurement
- > Insulation resistance
- > IEC lead test
- > Protective conductor current
- > Touch current
- > Load power/current
- > Alternative leakage current
- > Point to point testing of earth continuity and insulation resistance
- > RCD test
- > Power socket test



SEAWARD
GMC-INSTRUMENTS GROUP

Apollo+ Series

The best downloadable PAT testers on the market.



Apollo 600+

Apollo 600+ revolutionises safety management, with a built-in risk assessment tool for any workplace hazard and a variety of testing and inspection reports including portable appliance testing, fire detection and emergency lighting; Apollo 600+ offers an all-in-one solution to managing a risk-based approach to health and safety in any workplace, reducing the burden and ensuring compliance.

For complete traceability of results, including proof of visual inspection, the Apollo 600+ features an on-board camera, allowing photographs to be stored alongside risk assessments and other test and inspection data.




Apollo 500+

A great value 'plug and play' PAT tester with a comprehensive range of tests and advanced data transfer and storage features.

Designed to enable simple, professional and fast PAT testing, with remote data transfer, USB upload/download and a memory to store up to 10,000 complete test sets.

With point-to-point measurement, fast boot-up and a risk-based retest calculator to quickly determine suggested retest periods, Apollo 500+ is the ideal companion for high-volume testing.



Apollo 400+

A comprehensive range of electrical safety tests ensure compliance with the IET 4th Edition Code of Practice, whilst remote data transfer and USB download makes data management easy and efficient.

The Apollo 400+ is ideal for mid-volume PAT testing where detailed records are required.

Streamline the PAT testing process further by using the Apollo 400+ with a compatible label printer, barcode scanner and PATGuard 3 software.

Apollo 600+

Key Features:

- > On board camera
- > Upload data for faster retesting
- > Store 2,000 images
- > Store up to 50,000 appliance records
- > Ability to use (2D) QR codes
- > Built in universal and electrical risk assessment tools
- > Additional health and safety certificates

Apollo 500+

Key Features:

- > Store up to 10,000 appliance records
- > Upload data for faster retesting
- > Ability to use (2D) QR codes
- > Built in electrical risk assessment tool with suggested retest period calculator
- > User configurable tests - for non-electrical tests and inspections e.g. fire extinguishers and PPE

Apollo 400+

Key Features:

- > Store up to 2,000 appliance records
- > Printer Compatible
- > Point to point measurement (Rpe & IR) - needs optional accessory
- > 25 User configurable electrical test/visual inspections sequences

To see the **Apollo+** Series for yourself, request your live online demonstration today at seaward.com/apolloplus

T: +44 (0) 191 587 8741 E: sales@seaward.com

TESTED, TRUSTED... WORLDWIDE.



SEAWARD
GMC-INSTRUMENTS GROUP

Apollo+ Series

The best downloadable PAT testers on the market.

Comparison Chart:

General Features	600+	500+	400+
Battery & mains powered	●	●	●
Colour screen & QWERTY keypad	●	●	●
Large internal memory	up to 50,000 records and 2,000 photos	up to 10,000 records	up to 2,000 records
Bluetooth scanner & printer compatible	●	●	●
Password controlled user accounts	●	●	
Set up multiple user accounts with varying levels of privileges	●	●	
Clone facility to set up multiple testers	●	●	
Checkbox supplied as standard	●	●	
Test Inspection Features	600+	500+	400+
Auto-increment asset ID	●	●	
PAT Setup option to allow for custom menus	●	●	
Enter asset description after test using keypad or barcode scanner	●	●	●
Comprehensive electrical safety test features	●	●	●
Point to point measurement (Rpe & IR)	●	●	Optional accessory required
User configurable electrical test/visual inspection sequences	100	100	25
User set sites & locations	100	100	50
Risk based retest period calculator	●	●	
User definable comments lines against test records	4	4	
Configurable checklists for any workplace test or inspection (user tests)	●	●	
On-board camera	●		
Universal risk assessment	●		
Health & safety certificates	●		
Data Transfer	600+	500+	400+
1D and 2D Scanner connectivity	●	●	● Reads 1D Data Only
Read QR code (2D) labels with 2D scanner	●	●	
RFID reader connectivity	●		
Print Pass & Fail labels with 1D barcode	●	●	●
Print Pass & Fail labels with QR code (2D)	●	●	
Add your company logo to labels (on large 1D labels only)	●	●	
Select from various label formats to print	6	6	6
Download to PC via USB cable	●	●	●
Data Transfer via USB flash drive	●		
Filter results to be downloaded	●	●	●
Upload previous results to tester for retest	●	●	

To see the **Apollo+** Series for yourself, request your live online demonstration today at seaward.com/apolloplus



SEAWARD
GMC-INSTRUMENTS GROUP

T: +44 (0) 191 587 8741 E: sales@seaward.com

TESTED, TRUSTED... WORLDWIDE.

Apollo+ Series

The best downloadable PAT testers on the market.

Technical Specification:

Earth Continuity (Rpe)

Test Current: +/- 200mA DC
Measurement Range: 0.05Ω to 19.99Ω
Pass Value: User defined

Insulation Resistance (IR)

Test Voltage: 500V / 250VDC @ 1mA nominal
Measurement Range: 0.10MΩ to 19.99MΩ
Pass Value: User defined

IEC Lead Test

Test Voltage: 5VAC nominal
Test: Live / Neutral Checks for o/c, s/c and crossed polarity

Protective Conductor Current/Load

Test Voltage: Supply voltage, maximum load current 16A
Measurement Range: 0.25mA to 19.99mA
Pass Value: User defined

Touch Current

Test Voltage: Supply voltage, maximum load current 16A
Measurement Range: 0.10mA to 5.0mA
Pass Value: User defined

Load Power/Current

Test Voltage: 230V +10%, -15%, maximum load current 16A
Test Duration: Programmable up to a maximum of 240s
Measurement Range: 0.50A to 16.0A

Substitute (Alternative) Leakage Current

Test Voltages: >25VAC <50VAC
Measurement Range: 0.20mA to 19.99mA
Pass Value: User defined

RCD Test

Test Voltage: 230V +10%, -15%
Test Current: 30mA / 150mA rms sinusoidal
Display Range: 0ms to 2000ms
Test Method: Internal isolation to avoid tripping distribution board RCD

Power Socket Test

Voltage Range: 207V – 253VAC
Indicates configuration of voltage potential:-
Line potential phase to earth
Line potential phase to neutral
Line potential neutral to earth

General

Memory size (Apollo 600+): up to 50,000 records & 2,000 photos
Memory size (Apollo 500+): up to 10,000 records
Memory size (Apollo 400+): up to 2,000 records
Weight: 1.5kg
Dimensions: 230mm x 150mm x 100mm
Power Source: Mains or rechargeable battery pack

What's in the box?

(Supplied as standard with Apollo+ Series)

	600+	500+	400+
Apollo Instrument	1	1	1
Professional Carry Case	1	1	
Test Lead 1.2m with Alligator Clip, Red	1	1	1
Test Lead 1.2m with Alligator Clip, Black	1	1	
IEC Extension Lead, 0.5m	1	1	1
Black Mains Lead	1	1	1
USB Download Lead	1	1	1
Apollo+ Check Box	1	1	
Calibration Certificate	1	1	1
Quick Start Guide	1	1	1



To see the **Apollo+** Series for yourself, request your live online demonstration today at seaward.com/apolloplus



SEAWARD
GMC-INSTRUMENTS GROUP

T: +44 (0) 191 587 8741 E: sales@seaward.com

TESTED, TRUSTED... WORLDWIDE.

Apollo+ Series

The best downloadable PAT testers on the market.

Part Numbers:

Instrument Only

Apollo 600+	380A926
Apollo 500+	380A928
Apollo 400+	380A930

Optional Accessory Kits (Supplied without Apollo+ Instrument)

Elite Accessory Bundle (includes Test n Tag Elite 2 Printer, Bluetooth 2D Scanner, 2x Elite durable labels 25mm, 2x Elite durable labels 75mm, Apollo Kit carry case, 110V test adaptor.	380A9912
---	----------

Pro Accessory Bundle (includes: Test n Tag Pro Printer, Bluetooth Pro Barcode Scanner), 2x Pro labels 25mm, 2x Pro labels 75mm, Apollo Kit carry case, 110V test adaptor.	380A9911
--	----------

Optional Accessory Kits (Supplied with Apollo+ Instrument)

Apollo 600+ with Elite Bundle	380A9893
Apollo 500+ with Elite Bundle	380A9899
Apollo 400+ with Elite Bundle	380A9906

Apollo 600+ with Pro Bundle	380A9890
Apollo 500+ with Pro Bundle	380A9896
Apollo 400+ with Pro Bundle	380A9902

Optional Accessories

Test n Tag Elite 2 Bluetooth printer	339A989
Test n Tag Elite 2 Durable Label Rolls (52x74mm) approx. 120 off	339A9491
Test n Tag Elite 2 Durable Label Rolls (52x25mm) approx. 304 off	339A9490
Test n Tag Pro Bluetooth printer	339A980
Roll of Large White Label Rolls (52x74mm) approx. 130 off	339A946
Roll of Small White Label Rolls (52 x 25mm) approx. 350 off	339A947

Bluetooth 2D Elite Scanner	339A925
Bluetooth 1D Pro Barcode Scanner	339A923

110V Test Adaptor (for Rpe and IR)	270A076
3 Phase Leakage Adaptor, Star 5 pin 16A (for Rpe and Leakage)	391A920
3 Phase Leakage Adaptor, Star 5 pin 32A (for Rpe and Leakage)	391A910
3 Phase Adapter, Delta 4 pin 16A (for Rpe & IR)	209A910
3 Phase Adapter, Star 5 pin 16A 415V (for Rpe & IR)	209A911
3 Phase Adapter, Delta 4 pin 32A 415V (for Rpe & IR)	209A912
3 Phase Adapter, Star 5 pin 32A 415V (for Rpe & IR)	209A913

Apollo+ Series Checkbox	380A953
Apollo+ Series USB Download Lead	396A976
Apollo+ Series 0.5m IEC Test Lead	300A002
Apollo+ Series Red and Black Test Lead Set	380A951
Apollo+ Series Red Test Lead	380A982
Apollo+ Series Black Test Lead	380A983

Apollo+ Series Spare Battery	380A019
Apollo+ Series Battery Charger	380A9910
Apollo+ Series Kit Bag	71G109
Apollo+ Series Carrying Case	380A952

PATGuard Cloud


Details and free trial available at patguardcloud.com

Training

Seaward offer a range of PAT testing courses, go to www.seaward.com/training for more information.

Warranty

2 year warranty (subject to terms and conditions, available at www.seaward.com/warranty24)



To see the **Apollo+** Series for yourself, request your live online demonstration today at seaward.com/apolloplus



SEAWARD
GMC-INSTRUMENTS GROUP