SEAWARD

# **DO7010**

# Rugged portable micro ohmmeter for low resistance measurement

The DO7010 is a very rugged and very compact, portable digital ohmmeter for the measurement of low resistance. Using rechargeable and replaceable NiMh batteries with external charger, the DO7010 is capable of measuring with a current of 1 and 10A on all except the highest range.

The DO7010 has been designed with the latest solid state and microprocessor techniques to ensure the very best in measurement reliability and features. The LCD graphic display panel gives full information regarding the measurement configuration, and a single measurement start button ensures that the operation is simple and easy to use.

The measurement may be triggered when the measurement leads are applied to the device under test, ensuring fast single-person operation. The data-logging function also permits up to 1,000 date and time stamped readings to be stored.



#### **Key Features**

- True 4 wire measurement eliminates lead resistance errors
- 4 ranges  $6m\Omega$  to  $6\Omega$
- Resolution 1μΩ on 6mΩ range
- Graphics Display with backlight
- 3 languages (English, French, German)
- 1 and 10A measuring current even on the 600mΩ range
- Forward and reverse current measurement
- Auto average of forward and reverse measurement
- True zero offset
- Built in test resistor for confidence check
- Data logging with up to 1000 readings stored with date and time stamp
- Hi-Lo limits with audible and visual warning
- Automatic measurement trigger when leads are connected to DUT
- Small size and light weight <4Kg
- RS232 interface with option remote terminal to enable operation up to 15m distance
- Rechargeable NiMh batteries with charge indicator and easily replaceable battery pack

### **Ideal For**

- Aerospace
- Automotive
- Military
- Manufacturing
- Utilities, electrical, water and gas



# **Technical Specifications**

Range	Resolution	Typical Current	FSV	Accuracy at 20°C±5°C 1 year
6Ω	1mΩ	100mA/1A	±(0.1% Rdg +0.1% FS)	40ppm Rdg + 30ppm FS
600mΩ	100μΩ	1/10A	±(0.1% Rdg +0.1% FS)	40ppm Rdg + 30ppm FS
$60m\Omega$	10μΩ	1/10A	±(0.1% Rdg +0.1% FS)	40ppm Rdg + 30ppm FS
$6m\Omega$	1μΩ	1/10A	±(0.1% Rdg +0.1% FS)	40ppm Rdg + 30ppm FS

#### Measurement

4 Terminal Kelvin/Thomson principle eliminates errors due to lead resistance. Open circuit measurement voltage = 5VDC

#### Display

240 x 64 dot graphics LCD with backlight

#### Ranges

4 ranges with auto range mode. Two selectable measuring currents for each range

#### Terminals

The measurement leads are connected via Jaeger connectors and a full range of lead configurations are available

#### **Working Temperature**

0 to +50°C rel. humidity up to 80% non condensing

#### **Storage Temperature**

-20 to +50°C

#### Safety

Conforms to EN 61010-1, Main instrument Class III (SELV), Battery pack Class III (SELV) and external mains charger Class II

## **General Specifications**

# Battery

The DO7010 is supplied with battery fitted. The batteries are NiMh and the charger is external. The battery pack may be removed from the front panel when discharged and a replacement charged pack inserted. This ensures minimum down-time when making measurements

#### Lead Sets

We offer a wide variety of lead sets with 3 sizes of Kelvin clip or handspikes. Lead lengths may be up to 100m total loop

#### Data Logging

The DO7010 has data logging modes. The first will store each reading with record number date and time. The second is a sequence mode which will store values with operator ID, serial number etc

DO74A Plus Optional Accessories					
Part Number	Item	Part Number			
D07010-BP	Additional battery pack	100123			
HS01-7010	Duplex handspikes with 3m lead length	190052			
HS02-7010	Duplex handspikes with 3 and 15m lead length	190056			
LS03-7010	Lead set with 3m leads and terminated with large Kelvin clips type KC3	190043			
LS04-7010	Lead set with 3 and 15m lead length terminated in large Kelvin clips type KC3	190047			
MTS3	Calibration Standard	930242			
RSL04	RS232 interface cable 1m	920069			

#### **Dimensions**

390 x 160 x 270mm / 15 x 6.3 x 11" (w x h x d) approx

#### Mass 4kg / 9lbs approx

#### Services

1 year warranty (subject to product registration with Seaward. Visit www.seaward.co.uk/register-product)

Service and calibration by Calibrationhouse. Go to **www.calibrationhouse.com** for more information.

Part Number 930217

www.seaward.co.uk/DO7010 For USA, Canada and Mexico enquiries Tel: +1 (813) 886 - 2775 For all other enquiries Tel: +44 (0) 191 587 8741 Email: sales@seaward.co.uk