Solar Utility Pro

The only 1500V, 40A string checker.



The new **Solar Utility Pro** from Seaward takes PV testing to the next level. With the introduction of more efficient 1500V modules and inverters, Seaward have answered the industry call for an easy to use and robust tester with 1500V capabilities.

Its market leading 40A current capability enables the **Solar Utility Pro** to test parallel wired strings up to a maximum of 1500V / 40A, eliminating the time consuming task of separating strings to keep within lower limits of other instruments.

A single press of the Test button will give values for Open Circuit Voltage and Short Circuit Current, and when paired with the Seaward Solar Survey 200R irradiance meter, will also record irradiance, module and ambient temperature measurements. The large internal storage memory can record up to 999 complete record sets, which can be downloaded as a CSV file to a PC for review.

To make on site testing easier, the **Solar Utility Pro** is supplied with 1.5M long conversion leads that convert the standard MC4 leads to alligator clips – particularly useful in combiner boxes and junction boxes.

These features, in a rugged enclosure, give the larger scale PV engineer the most efficient, portable and highest rated tester available.

To see the new **Solar Utility Pro** for yourself, request your live online demonstration today at **seaward.com/SUP**

T: +44 (0) 191 587 8741 E: sales@seaward.com TESTED, TRUSTED... WORLDWIDE.





Why buy the Solar Utility Pro?

- > Test up to 1500V / 40A systems – ideal for today's more modern powerful PV installations
- > Highest rated PV tester on the market – minimizing accidental damage to the instrument or the user by testing across multiple strings
- Record up to 999 full sets of string data – maximizing time in the field to complete testing without downloading and clearing the memory
- > Rugged case design giving more protection while being transported around large utility scale sites
- Contact us for product training and support



Solar Utility Pro

The only 1500V, 40A string checker.



Key Features:

- 1500V / 40A rated >
- > Large display designed for reading in direct sunlight
- > Direct MC4 connections, with the option to add a conversion lead set for safer connections in combiner boxes
- > Simple single button test
- > Rugged case designed for continuous site work
- Store up to 999 complete record > sets
- > CSV output to PC to review data
- > Pairs to Solar Survey 200R irradiance meter to capture the irradiance and temperature measurements at the time to test (single person testing)

Kit includes:

- Solar Utility Pro unit >
- Set of 1.2M red and black MC4 leads > with test probe and aligator clip
- > Set of 2M red and black MC4 extension leads
- > SS200R irradiance meter
- SS200R irradiance meter clamp >
- PV hold-all bag >
- 3 x 18650 protected lithium-ion > batteries
- > Battery charger
- 2 x Dust covers >
- 1 x UK mains lead >
- > 1 x Schuko mains lead





Seaward Solar Cert Software

- > Compatable with Solar Cert to give you the ability to compare expected values calculated using the panel parameters
- missing, Solar Cert now has an



To see the new Solar Utility Pro for yourself, request your live online demonstration today at seaward.com/SUP

T: +44 (0) 191 587 8741 E: sales@seaward.com TESTED, TRUSTED... WORLDWIDE.

SEAWARD

Solar Utility Pro

The only 1500V, 40A string checker.



Technical Specification:

Open Circuit Voltage Measurement (PV Terminals)

Display Range Measuring Range Resolution Accuracy **Short Circuit Current Measurement** Display Range Measuring Range Maximum Power Resolution Accuracy **General Specifications** Dimensions

Weight Power Source Communication Display On-board Memory Storage Environment Operating Conditions Environmental Protection

Connectivity

USB download to PC, via DataLogger Utility Wireless "Solarlink" to Survey 200R 0.0VDC - 1500VDC 5.0VDC - 1500VDC 0.1VDC max ±(0.5% + 2 digits)

0.00ADC - 40.00ADC 0.50ADC - 40.00ADC 45kW 0.01ADC ±(1% + 2 digits)

340mm x 300mm x 152mm (L x W x H, Closed) 13.4" x 11.8" x 6.0" (L x W x H, Closed) 4.7kg (10.4lbs) 3x 3.7V / 3000mAh Li-ion batteries USB Download

Custom LCD with backlight Up to 999 datasets -25°C to +65°C (-13°F to 149°F) 0°C to 40°C (32°F to 104°F) IP 40 open, IP64 closed

(CSV format) Frequency 433MHz, range 30m/100ft (ROW) Frequency 915MHz, range 30m/100ft (USA)

Part Number: 416A910 (433MHz, ROW), 416A912 (915MHz, USA Only)



SEAWARD

To see the new **Solar Utility Pro** for yourself, request your live online demonstration today at **seaward.com/SUP**